

LIGHTOVER Tunic with sleeve(s) (PPE - category III)



FIELD OF APPLICATION

The LIGHTINOX tunic is made with 100% food contact approved stainless steel. It is used by butchers in meat industries, Horeca, supermarkets and many other fields such as textile industry... It ensures cut-protection against any risks with hand knives, hand cutting tools or stabbing.

MATERIAL: Stainless steel chainmail. Food contact

FEATURES


Bust:

- Wire diameter: 0,7 mm
- Internal diameter of the rings: 5,6 mm
- External diameter of the rings: 7 mm

Sleeve(s):

- Wire diameter: 0,5 mm
- Internal diameter of the rings: 3 mm
- External diameter of the rings: 4 mm

Straps attached to the tunic with stainless steel plates
Adjustable waist belt and back strap 100 % polyurethane (food contact according to EU regulation 10/2011) and polyacetal buckles.
Equipped with 2x3 press studs in order to adapt a MANULATEX chainmail shoulder glove.
Possibility to add a press-studs apron or a cover for maximum hygiene and ease of cleaning.



NORMS & REGULATIONS

This tunic complies with the regulation (UE) EPI 2016/425 (2016).

Bust: EN ISO13998 (2003) performance level 2: suitable for boning operations.

Sleeve(s): EN ISO13998 (2003) performance level 1: suitable for boning operations.

Notified body in charge of the certification: N° 0556 Prüf und Zertifizierungsstelle Nahrungsmittel und Verpackung - Fachbereich Nahrungsmittel - Lortzingstrasse 2 - D - 55127 Mainz

Notified body involved in manufacturing control: N° 0333 AFNOR certification
11 rue Francis De Pressensé - 93571 - La Plaine Saint-Denis



CLEANING CONDITIONS

Cleaning / Disinfection: PPE can be cleaned using a suitable washing gun, by soaking, by vigorous brushing or in a washing machine. In all cases, the water with added product must be at a maximum temperature of 63 °C.

Warning : the technical sheet of the product used refers to a maximum water temperature, which may be lower.

Particular attention to dosage and temperature must be observed in the case of using alkaline chlorinated or acidic products.

Use only products authorized by the veterinary services. The use of chlorine in large doses and at high temperature is not recommended.

Disinfection: High temperature disinfection can be done with clean water of a minimum of 82 °C up to a maximum temperature of 90 °C, in a machine, by soaking or sprinkling.

Drying and Storage: Forced drying by hot or natural air ventilation but in a dry and ventilated place. Store in a cool, dry place

SIZE AND REFERENCES: * Height from top of the shoulder

References left sleeve 65 cm	OXLI650.7M3.130XG5	OXLI650.7M6.130XG5
References right sleeve 65 cm	OXLI650.7M3.130DX5	OXLI650.7M6.130DX5
References two sleeves 65 cm	OXLI650.7M3.130DG5	OXLI650.7M6.130DG5
Width x height (cm)*	55 x 95	55 x 110
Operator's size (cm)	158 - 190	165 - 220
Chest measurement (cm)	90 - 120	90 - 120

N° intrastat : 73239390

Bien plus que la sécurité
More than just safety



Adresse postale : CS 40055 - 49170 - SAINT-GEORGES-SUR-LOIRE - France - E-mail : manulutex@manulutex.fr - Internet : www.manulutex.fr
Site de Champtocé-sur-Loire : 1 Rue du Mille - 49123 CHAMPTOCÉ-SUR-LOIRE - France - Tel : +33 (0)2 41 39 90 30 -
Site de St-Germain-des-Près : Zone Artisanale La Potherie - 49170 ST-GERMAIN-DES-PRÉS - Tel : +33 (0)2 41 39 90 30
SAS au capital de 125 000 € - R.C.S. Angers B 332 107 036 (85 B 112) - Siret 332 107 036 00029 - APE 3299Z - TVA FR 73 332 107 036 - EORI FR 332 107 036 00029