

JULIET APRON

PPE - category I



FIELD OF APPLICATION

JULIET apron is resistant to standard cleaning agents. It is appreciated for its flexibility, light weight and excellent tear resistance. Temperature range for use: -30°C to +90°C.

CLEANING CONDITIONS

Cleaning : wash and brush the apron in hot soapy water (40°C) or in a mixture of water and a gentle detergent. **Rinsing** : with water. Do not use toxic products to clean or rinse the apron. **Storage** : After cleaning, store in a dark, dry, well-ventilated place. The apron must be replaced when it shows signs of wear and tear.

With a proper use and a good maintenance, your apron lasts longer!

PERFORMANCE LEVELS

Type of test	Standard	Performance
Abrasion resistance	EN 12947-2	>100 000 frictions
Trapezoidal tear resistance	EN ISO 9073-4	>40 N
Tensile resistance	EN ISO 13934-1	>140N
Puncture resistance	EN 863	>20N

MATERIAL

polyurethane on polyamide support

FEATURES

- Colours : white, red, yellow, navy blue and khaki green
- Thickness : 400 µm (± 10%)
- Weight : 170 g/m² (± 10%)
- Standard dimensions (width x height in cm) : 90x115

Aprons with stainless steel brass rings and eyelets.

Food safe polypropylene adjustment loop

Detectable plastic hook and polyester braided elastic

NORMS AND REGULATIONS

Base material in accordance with **EC N° 1935/2004 Regulation**, articles 3 and 4 on materials and articles intended to come into contact with food.

Base material in accordance with **UE N°10/2011 Regulation** on rubber materials and articles intended to come into contact with food. This PPE may be put in fortuitous contact with all types of food.

Apron in accordance with **Article 33 of the REACH Regulation N°1907/2006** and its amendments on products containing SVHC.

This apron complies with the regulation **(UE) PPE 2016/425** and the standard **NF EN ISO 13688 (2013)**.

Claimed mechanical properties: abrasion, tear, tensile and puncture resistance.

