

BRAVO APRON

PPE - category I



MATERIAL

Polyester canvas coated on both sides with nitrile

FEATURES

- Colours : white, yellow, brown, blue, green
- Thickness : 500 µm (± 10%)
- Weight : 600 g/m² (± 10%)
- Standard dimensions (width x height in cm) : 90x115

Aprons with stainless steel brass rings and eyelets

For **standard and harness** aprons fittings :

- Food safe polypropylene adjustment loop(s)
- Detectable blue plastic hook and polyester braided elastic

For **automatic** aprons fittings :

- Sewn straps made of nitrile, both sides coated on polyester support
- Stainless steel rivets and rings

NORMS AND REGULATIONS

Base material in accordance with Regulation **EC N° 1935/2004** on materials and articles intended to come into contact with food and **EU Regulation N° 2023/2006** on good manufacturing practice for materials and articles intended to come into contact with food.

Basic material in accordance with the **decree of August 5, 2020** relating to rubber materials and objects intended to come into contact with foodstuffs and pacifiers for infants and young children. This material is not intended for oral contact as described in appendix III and IV.

This PPE may be put in fortuitous contact with aqueous, acidic and fatty food (Correction factor 4)

Apron in accordance with Article 33 of the **REACH Regulation N°1907/2006** on products containing SVHC and its amendments.

Does not contain phthalate, silicone (and silicone derivatives), or bisphenols.

This apron complies with the regulation **(UE) PPE 2016/425** and the standard **NF EN ISO 13688 (2013)**.

Claimed mechanical properties: abrasion, tear, tensile and puncture resistance.



FIELD OF APPLICATION

BRAVO apron is suitable for use in the food industry (high resistance to animal fats, blood and temperature). BRAVO apron is a reusable PPE (Personal Protective Equipment) offering a level of protection against mechanical risks and offering a level of resistance to water penetration. Temperature range for use: -15°C to +80°C.

CLEANING CONDITIONS

Cleaning : wash and brush the apron in hot soapy water (40°C) or in a mixture of water and a gentle detergent. **Rinsing** : with water. Do not use toxic products to clean or rinse the apron. **Storage** : After cleaning, store in a dark, dry, well-ventilated place. The apron must be replaced when it shows signs of wear and tear.

With a proper use and a good maintenance, your apron lasts longer !

PERFORMANCE LEVELS

Type of test	Standard	Performance
Abrasion resistance	EN 530 méthode 2	>2000 cycles
Trapezoidal tear resistance	EN ISO 9073-4	>50 N
Tensile resistance	EN ISO 13934-1	>700N
Puncture resistance	EN 863	>50N