

## JULIET OVERSLEEVES



### FIELD OF APPLICATION

JULIET oversleeves are resistant to standard cleaning agents. They are appreciated for their flexibility, light weight and excellent tear resistance.

### CLEANING CONDITIONS

**Cleaning** : wash and brush the apron in hot soapy water (40°C) or in a mixture of water and a gentle detergent. **Rinsing** : with water. Do not use toxic products to clean or rinse the oversleeves. **Storage** : After cleaning, store in a dark, dry, well-ventilated place. The oversleeves must be replaced when they show signs of wear and tear.

**With a proper use and a good maintenance, your oversleeves last longer!**

### MATERIAL

Polyurethane on polyamide jersey support

### FEATURES

- Colours :white, red, yellow, navy blue and khaki green
- Thickness : 400 µm (± 10%)
- Weight : 170 g/m<sup>2</sup> (± 10%)
- Standard dimensions : length 40 cm

**Wrist fastening : neoprene (3 mm thick)**

**Biceps fastening by polyester elastic.**

### NORMS AND REGULATIONS

Base material in accordance with **EC N° 1935/2004 Regulation**, articles 3 and 4 on materials and articles intended to come into contact with food\*.

Base material in accordance with **UE N°10/2011 Regulation** on rubber materials and articles intended to come into contact with food. This PPE may be put in fortuitous contact with all types of food\*.

Oversleeves in accordance with **Article 33 of the REACH Regulation N°1907/2006** and its amendments on products containing SVHC\*.

(\* ) with the exception of neoprene wrist fastening.

